

KVSW44TN, Mechanical Connector with Spacer Bar

By Burndy

Catalog # [KVSW44TN](#)

Mechanical Connector For CUWeld and Copper Supplied with a CU alloy Spacer that separates run and tap conductors, Run: 500-1000 Kcmil, Tap: 250-1000 Kcmil.



Features

- Compact, 2-piece, high strength, high copper alloy, recommended for heavy duty connections
- High copper alloy spacer bar separates run and tap conductors
- Provides high contact pressure, confines conductor strands and assures vibration-proof connection
- Longer peened bolt permits swivel action for easier installation
- Neoprene rings hold silicon bronze bolts in place during installation
- Installed with ordinary wrench

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	500 kcmil- 1000 kcmil
Conductor Type	CU C Str-Size
Conductor - Copper Str Tap Range	250 kcmil - 1000 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	105.15 mm
Dimension - Height inch	4.14 in
Package Weight	0.000 lb.
Dimension - Width inch	1.56 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - Length Overall inch	1.04 in
Dimension - Stud Size inch	5/8 in

General

Plated	Y
Trade Name	OKLIP™
UPC	781810245934
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810245934
UPC 14 Digit GTIN	00781810245934

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)