



GC4C4CW, Mech Ground, Two Cables to Bar, Tin Plated

By Burndy
Catalog # [GC4C4CW](#)

Mechanical Grounding Connector, 2 Cables to 1/4" Thick Bar, 8 AWG (Sol)- 4 AWG (Str), 3/8" Stud, Heavy Tin Plated



Features

- High copper alloy ground connector for joining a wide range of 2 parallel cables to 1/2" thick bar
- Type GC separates cable from bar
- Type GCM clamps cable direct to bar surface
- One wrench installation
- UL467 Listed
- Suitable for Direct Burial in earth or concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor - Copper Solid Size Range	8 AWG-4 AWG
Conductor - Copper Str Size Range	8 AWG - 4 AWG
Conductor - Copper Str Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	37.8 mm
Length	0.88 in
Dimension - Height inch	1.49 in
Package Weight	0.000 lb.
Dimension - Width mm	28 mm
Dimension - Width inch	1.12 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	22 mm
Height	1.49 in
Width	1.12 in
Dimension - Width fraction	1-1/8 in
Dimension - Length Overall inch	0.88 in
Dimensions	0.88 in x 1.12 in x 1.49 in

Force Related

Installation Torque	240 lb-in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
UPC	781810117279
Material Type - Screw	DURIUM™ Silicon Bronze
Material	Copper
Plating Type	Heavy Tin Plated
UPC 12 Digit	781810117279
UPC 14 Digit GTIN	00781810117279

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)