



GD1926, Mech Ground, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GD1926](#)

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 4 AWG (Sol.) - 2/0 AWG (Str.), 2-1/2" Rod, 2-1/2" Pipe.

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Application

For Joining A Range Of Two Parallel Copper Cables To Rod Or Pipe And Burial In Ground Or Concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor - Copper Solid Size Range	4-2/0
Conductor - Rod Size Range	2 1/2 in
Conductor - Copper Str Size Range	4-2/0
Conductor - Copper Str Size	• 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor - Rod Size	2 1/2 in



Conductor - Copper Str Size B Range	2.5
Conductor - Copper Tube Std Size Range	2-1/2
Conductor - Copper Tube Std Size	2-1/2

Dimensions

Package Height	0.000 in
Dimension - Height mm	127 mm
Dimension - Height inch	5.00 in
Dimension - Height fraction	5 in
Package Weight	0.000 lb.
Dimension - Width mm	106 mm
Dimension - Width inch	4.19 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.38 in
Dimension - Width fraction	4-1/4 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Plated	N
Sub Brand	MECHANICAL CONNECTOR
UPC	781810260364
Type	GD
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	266
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810260364
UPC 14 Digit GTIN	00781810260364

Logistics

Pallet Quantity	1200
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)