



Crimper, Installs #14-4/0 AWG, BG & D3 Grooves

By Burndy
Catalog # [MD6](#)

HYTOOL™ Series, Hand-Operated Crimper, #14 - 4/0 AWG, BG and D3 grooves

Features

- Ergonomically designed, one-piece, composite polymer handles
- Comfort grip handles
- Time-proven steel jaw designs
- No tool adjustment required
- 99,000 crimp/cycle life
- Positive lock, spring loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Electroless nickel plated jaws and jaw links

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
Buy American Compliant	No

Conductor

Crimping Ranges	• Copper: 10 sol. - 500 Kcmil • Copper Flex: #8 to 350 kcmil
-----------------	--

Dimensions

Length	25.38 in
Weight	6.25 lb.
Height	2 in
Width	7.04 in



Dimensions	25.38 in x 7.04 in x 2 in
------------	---------------------------

Force Related

Crimp Force Capacity	4.5 ton
----------------------	---------

General

Application - For Use On	Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors
Trade Name	HYTOOL™
Sub Brand	HYTOOL
Series	HYTOOL™ Series
Tool Type	Hand Operated Crimper
Product Type	4.5-Ton
Die Type	W Die and X Die
UPC	781810446003
UPC 12 Digit	781810446003
UPC 14 Digit GTIN	00781810446003

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)