



Crimper, Installs #14-4/0 AWG, Permanent D3 Groove

By Burndy
Catalog # [MD66](#)

HYTOOL™ Series, Hand-Operated Crimper, #14 - 4/0 AWG, Permanent D3 Groove

Features

- Ergonomically designed, one-piece, composite polymer handles
- Comfort grip handles
- Time-proven steel jaw designs
- No tool adjustment required
- 99,000 crimp/cycle life
- Positive lock, spring loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Electroless nickel plated jaws and jaw links

Application

Crimping

Specifications

Standards - RoHS Compliance Status	EX
Buy American Compliant	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Conductor

Crimping Ranges	• Taps: Copper: #10 sol. to 2/0 str., Aluminum & ACSR: #14 sol. to 4/0 ACSR • Stirrups: #6 to 4/0 ACSR • Overhead Full Tension Deadends, Full Tension Splices and Terminals: #10 str. to 4/0 ACSR • Installs Splices, Taps or Terminations: #8 to 500 kcmil Copper Stranded, #8 to 350 kcmil Copper Flex, #8 to 350 kcmil Aluminum
-----------------	--



Dimensions

Length	24.5 in
Weight	6.44 lb.
Height	2 in
Width	6.65 in
Dimensions	24.5 in x 6.65 in x 2 in

Force Related

Crimp Force Capacity	4.5 ton
----------------------	---------

General

Application - For Use On	Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors
Trade Name	HYTOOL™
Sub Brand	HYTOOL
Series	HYTOOL™ Series
Tool Type	Hand Operated Crimper
Product Type	4.5-Ton
Die Type	W Die and X Die
UPC	781810446102
UPC 12 Digit	781810446102
UPC 14 Digit GTIN	00781810446102

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[English\]](#)