



BURNDY

GD1929TN, Mech Ground Conn, 2 Cables to Rod/Pipe, Tin Plated

By Burndy

Catalog # [GD1929TN](#)

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 2/0 AWG (Sol.) - 250 kcmil, 2-1/2" Rod, 2-1/2" Pipe.



Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Certification - ETL

No

Certification - UL Recognized

No

Standards - Industry Standards Met

UL467
Standards - RoHS Compliance Status
CM
Certification - cULus
No
Certification - UL Listed Direct Burial
Yes
Industry Standard(s)
UL467
UL Listed
Yes
Certification - CSA Approved
No

Conductor

Conductor - Copper Solid Size

- 2/0
- 3/0
- 4/0

Conductor - Copper Solid Size Range

2/0-4/0

Conductor - Copper Str Size Range

2/0 AWG - 250 kcmil

Conductor - Copper Str Size

- 2/0
- 3/0
- 4/0
- 250

Conductor - Copper Str Size B Range

2.5

Conductor - Copper Tube Std Size Range

2-1/2

Conductor - Copper Tube Std Size

2-1/2

Dimensions

Package Height

0.000 in

Dimension - Height mm

0 mm

Package Weight

0.000 lb.

Dimension - Width mm

106 mm

Dimension - Width inch

4.19 in

Package Length

0.000 in

Package Width

0.000 in

Dimension - B Length inch

1.38 in

Dimension - Width fraction

4-1/5 in

Force Related

Installation Torque Recommended in-lb

240 LBS/in

General

Plated

Y

UPC

781810117361

Material Type - Screw

DURIUM™ Silicon Bronze

U Bolt Type

266

Material

Copper Alloy, Cast

Plating Type

Tin Plated
UPC 12 Digit
781810117361
UPC 14 Digit GTIN
00781810117361

Product Assets

[Catalog.\[English\]](#)



A Hubbell brand
© 2026 Hubbell Incorporated. All rights reserved
BRDY_CA-GD1929TN-SPEC-EN | REV 5/2026