



GD1929W, Mech Ground Conn, 2 Cables to Rod/Pipe, Tin Plated

By Burndy
Catalog # [GD1929W](#)



2 Parallel Copper Cables to Rod or Pipe, Accommodates: 2/0 Sol-250 kcmil Cu Cables, 2-1/2" - 2-7/8" Rod, 2-1/2" IPS, Hot Tin Plate

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 2/0 • 3/0 • 4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	2/0 AWG - 250 kcmil
Conductor - Copper Str Size Range	• 2/0 • 3/0 • 4/0 • 250
Conductor - Copper Str Size B Range	2.5
Conductor - Copper Tube Std Size Range	2-1/2

Conductor - Copper Tube Std Size	2-1/2
----------------------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Dimension - Width mm	106 mm
Dimension - Width inch	4.19 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.38 in
Dimension - Width fraction	4-1/5 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Plated	Y
UPC	781810117262
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	266
Material	Copper Alloy
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810117262
UPC 14 Digit GTIN	00781810117262

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)