



Crimper, Polymer Handles, #14-4/0 AWG, BG & D3 Grooves

By Burndy
Catalog # [MD7](#)

HYTOOL™ Hand-Operated Crimper, Polymer Handles, #14 - 4/0 AWG, BG & D3 grooves

Features

- Ergonomic designed, one-piece composite polymer handles
- Comfort grip handles
- Time-proven steel jaw design
- No tool adjustment required
- 99,000 crimp/cycle life
- Positive lock, spring-loaded die retainer buttons
- Permanent D3 die groove
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Electroless nickel plated jaws and jaw links

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Conductor

- Crimping Ranges
- Taps: Copper: #10 sol. to 2/0 str., Aluminum & ACSR: #14 sol. to 4/0 ACSR
 - Stirrups: #6 to 4/0 ACSR
 - Overhead Full Tension Deadends, Full Tension Splices and Terminals: #10 str. to 4/0 ACSR
 - Installs Splices, Taps or Terminations: #8 to 500 kcmil Copper Stranded, #8 to 350 kcmil Copper Flex, #8 to 350 kcmil Aluminum

Dimensions

Length	25 in
Weight	7 lb.
Height	2 in
Width	4.5 in
Dimensions	25 in x 4.5 in x 2 in

Force Related

Crimp Force Capacity	4.5 ton
----------------------	---------

General

Application - For Use On	Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors
Trade Name	HYTOOL™
Series	HYTOOL™ Series
Tool Type	Hand Operated Crimper
Product Type	4.5-Ton
Die Type	W and X Die
UPC	781810010914
UPC 12 Digit	781810010914
UPC 14 Digit GTIN	00781810010914

Logistics

Package Contents	Tool only
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)