



GG192W, Mech Ground, Cu Bar/Strap/Braid or Cable to Rod/Tube

By Burndy
Catalog # [GG192W](#)



Mechanical Ground Connector; Accommodates 2-1/2" IPS Tube, 2-1/2" to 2-7/8" Rod, 1/2" Hardware, Hot Tin Dipped

Features

- High copper alloy ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth of concrete
- UL467 Listed
- One wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• Rod-Size • CU Tube Std-Size
Conductor - Copper Str Size B Range	2.5
Conductor - Copper Tube Std Size Range	2-1/2-2-3/4
Conductor - Copper Tube Std Size	• 2-1/2 • 2-3/4

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - Height mm	127 mm
Dimension - Height inch	5.00 in
Package Weight	0.000 lb.
Dimension - Width mm	116 mm
Dimension - Width inch	4.56 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.75 in
Dimension - Width fraction	4-5/9 in
Dimension - Braid Width Max inch	2.00 in
Dimension - Braid Width Max fraction	2 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

Plated	Y
UPC	781810111574
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	232
Material	Copper Alloy
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810111574
UPC 14 Digit GTIN	00781810111574

Logistics

Minimum Pack Quantity	8
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)