



GP1526G1, Mech Ground Conn, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GP1526G1](#)

Raised Floor Grounding Clamp, #8 Sol. - 2/0 Str., 1.69 in L, 2.62 in W

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	#8 Sol AWG - 2/0 Str AWG
Number Of Conductors	• 1 • 2

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Dimension - Width mm	67 mm
Dimension - Width inch	2.62 in
Package Length	0.000 in
Package Width	0.000 in



Dimension - L Length Overall mm	43 mm
Dimension - B Length inch	1.75 in
Bolt Size	3/8 in
Dimension - Length Overall inch	1.69 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
Pedestal Type	Round
UPC	781810042823
U Bolt Type	UB244
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810042823
UPC 14 Digit GTIN	00781810042823

Logistics

Minimum Pack Quantity	1
Pallet Quantity	432
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)