


NA142N, Substation - Copper Terminal, 3/4" Cu Pipe, 2-Hole

By Burndy

Catalog # [NA142N](#)

Copper Bolted Terminal , Tube to Flat , 3/4" Cu Pipe , 2 Pad Holes , 230 kV.



Application

Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX
UL Listed	No
Certification - CSA Approved	No

Conductor

Number Of Conductors	1
Conductor - Connection Combination	Tube to Flat
Conductor Type	- CU Tube Std-Size - CU Tube EH-Size
Conductor - Copper Tube Std Size Range	3/4 IPS
Conductor - Copper Tube Std Size	3/4 IPS
Conductor - Copper Tube EH Size Range	3/4 IPS
Conductor - Copper Tube EH Size	3/4 IPS

Configuration

Physical Attribute - Pad Configuration	1.63 x 3 - 2 holes
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.63 in
Package Height	0.000 in
Dimension - Height mm	50.8 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	2.00 in
Dimension - Height fraction	2
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	133 mm
Dimension - Width mm	62 mm
Dimension - Width inch	2.44 in
Dimension - B Length inch	2.00 in
Dimension - D inch	3.00 in
Dimension - N inch	0.625 in
Dimension - Length Overall inch	5.25 in

General

Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Plated	N
Clamping Element Design	Body and Cap
UPC	781810002322
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810002322
UPC 14 Digit GTIN	00781810002322

Logistics

Pallet Quantity	720
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)