



HSB110H48PF5, Heat Shrink Tubing, Heavy, Black

By Burndy
Catalog # [HSB110H48PF5](#)

1.10" ID Min (Expanded), .35" ID Max (Recovered), 1-3/0, Polyolefin, Thick Wall, 48" Lengths, 5 Pieces

Features

- Heavy Wall Heat Shrink Tubing
- Shrink Ratio 3:1
- Inside diameter is coated with adhesive sealant to protect against moisture and corrosion
- Rated to 1500V
- UL486D Listed for Direct Burial

Application

For Direct Burial

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	1AWG - 3/0AWG
Conductor Range	#1 AWG to #3/0 AWG

Configuration

Connector Type	HEAVY WALL TUBES
----------------	------------------

Current

Voltage Rating	1500 V
----------------	--------

Dimensions

Package Height	4 in
Package Weight	28 lb.
Package Length	50 in
Package Width	4 in

General

Sub Brand	HEAT SHRINK
Product Type	Polyolefin Thick Wall Heat Shrink
UPC	781810214909
Type	HS-H-PF, Heavy Wall, Flame Retardant
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	1
Number of Pieces in Package	5
Pallet Quantity	36
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)