



HSB150H48PF5, Heat Shrink Tubing, Heavy Wall, Black

By Burndy
Catalog # [HSB150H48PF5](#)

1.5" ID Min (Expanded), .5" ID Max (Recovered), Thick Wall, Black, 4-Foot Length, 5-Piece package, 1500V

Features

- Heavy Wall Heat Shrink Tubing
- Shrink Ratio 3:1
- Inside diameter is coated with adhesive sealant to protect against moisture and corrosion
- Rated to 1500 V
- UL486D Listed for Direct Burial

Application

For Direct Burial

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	2/0AWG - 350kcmil
Conductor Range	#2/0 AWG - 350 Kcmil

Configuration

Connector Type	HEAVY WALL TUBES
----------------	------------------

Current

Voltage Rating	1500 V
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Sub Brand	HEAT SHRINK
Product Type	Polyolefin Thick Wall Heat Shrink
UPC	781810214916
Type	HS-H-PF, Heavy Wall, Flame Retardant
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	1
Number of Pieces in Package	5
Pallet Quantity	180
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)