



HSB200H12PF2, Heat Shrink Tubing, Heavy, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB200H12PF2](#)

2.0" ID Min (Expanded), .75" ID Max (Recovered), Heavy Wall, Black, Flame Retardant, 12" Piece, 2 per package

Features

- Heavy Wall Heat Shrink Tubing
- Shrink Ratio 3:1
- Inside diameter is coated with adhesive sealant to protect against moisture and corrosion
- 1500V
- UL486D Listed for Direct Burial

Application

For Direct Burial

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
Buy American Compliant	No
EU RoHS Indicator	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	250kcmil - 500kcmil
Conductor Range	250-500 Kcmil

Configuration



Connector Type	HEAVY WALL TUBES
----------------	------------------

Current

Voltage Rating	1500 V
----------------	--------

Dimensions

Package Height	6.00 in
Package Weight	5 lb.
Package Length	19.38 in
Package Width	7.00 in

General

Sub Brand	HEAT SHRINK
UPC	781810214879
Type	HS-H-PF, Heavy Wall, Flame Retardant
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	1
Number of Pieces in Package	2
Pallet Quantity	240
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)