




NA17A4N, Substation - Aluminum Bolted Terminal

By Burndy

Catalog # [NA14A4N](#)

Substation Connectors



Features

- Type NA-A Aluminum Terminals for Tube to Pad
- Properly proportioned to minimize conductor corrosion due to galvanic action
- When properly used, this item does not require use of bimetallic plates, contact Burndy Technical Support for recommendations
- One-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Tube Std Size Range	3/4 IPS
Conductor - AL Tube Std Size	3/4 IPS
Number Of Conductors	1
Conductor - Connection Combination	Tube to Flat
Conductor Type	• AL Tube Std-Size • CU Tube Std-Size
Conductor - Copper Tube Std Size Range	3/4 IPS IPS
Conductor - Copper Tube Std Size	3/4 IPS IPS

Configuration

Physical Attribute - Pad Configuration	4 holes
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - G inch	1.41 in
Dimension - Pad Width inch	4.00 in
Package Height	0.000 in
Dimension - Height mm	79.2 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	3.12 in
Package Weight	0.000 lb.
Dimension - Width mm	71 mm
Dimension - Width inch	2.80 in
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	165 mm
Dimension - B Length inch	3.25 in
Dimension - D inch	4.00 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	6.50 in

Force Related

Installation Torque	300 LBS/in
Recommended in-lb	

General

Plated	N
Material - Hardware	Aluminum
One Wrench Installation	Y
Clamping Element Design	Body and Cap
UPC	781810164853
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810164853
UPC 14 Digit GTIN	00781810164853

Logistics

Pallet Quantity	64
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)

