



HSIC81FR, Heat Shrink End Cap, Heavy Wall, Black

By Burndy
Catalog # [HSIC81FR](#)

2kV Rated, Fire Retardant, .5" ID Min (Expanded), .16" ID Max (Recovered), Thick Wall, 2.5" Long, Black

Features

- Heavy Wall Cross Linked Polyolefin
- UV94-V0
- Recognized Flame Retardant Material
- 3:1 Shrink Ratio
- Shrink Temperature of 150°C
- Blue Thermochromic lines disappear during correct installation
- Rated up to 2kV
- Sealing Adhesive
- Moisture and Water Resistant
- UL486D
- Insulates and Protects
- Direct Burial

Application

For Used To Insulating Exposed Conductors In Energized Applications

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Certification - CSA Approved	No

Conductor

Conductor Size	8AWG - 1AWG
Conductor Range	#4 AWG to #2/0 AWG

Configuration

Connector Type	HEAVY WALL END CAP
----------------	--------------------



Current

Voltage Rating	2000 V
----------------	--------

Dimensions

Package Height	40.25 in
Length	2.5 in
Package Weight	1.95 lb.
Package Length	9.00 in
Package Width	6.13 in
Height	0.5 in
Width	0.5 in
Dimensions	2.5 in x 0.5 in x 0.5 in

General

Color	Black
Sub Brand	HEAT SHRINK
Product Type	Heavy Wall Black Polyolefin Heat Shrink End Cap
UPC	781810266595
Type	Heat Shrink Tubing
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	10
Pallet Quantity	1000
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)