



HSTPMX06256IPK25, Thin Wall Polyolefin Heat Shrink Tubing, Mixed, 25-Pack, 6" Lengths, 5/8" ID

By Burndy
Catalog # [HSTPMX06256IPK25](#)

5/8 I.D., 1 Unit = 1 Pk Of 25, Color = Mixed, 2:1 Ratio, Thin Wall Polyolefin Heat Shrink, 600V Max, Shrink Temp 90°C Min, -55°C To 135°C Continuous Operating Temp, Store At 21°C.

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

General

Catalog Number	HSTPMX06256IPK25
Color	Multiple Colors



UPC	621945695115
-----	--------------

Logistics

Carton Quantity	16
-----------------	----

Product Assets

- [Brochures - Polyolefin Thin Wall Heat Shrink Brochure](#)
- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Distributor Promotion: HS-TP Thin Wall Polyolefin Heat Shrink Expires 12-31-2024](#)
- [Sales Drawings - 50139507](#)
- [Specifications - HSTPMX06256IPK25](#)



A Hubbell brand