




NA15A4NCG2, Substation - Aluminum Bolted Terminal

By Burndy
Catalog # [NA15A4NCG2](#)

Substation Connectors



Features

- Type NA-A Aluminum Terminals for Tube to Pad
- Properly proportioned to minimize conductor corrosion due to galvanic action
- When properly used, this item does not require use of bimetallic plates, contact Burndy Technical Support for recommendations
- One-wrench installation

Application

Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Tube Std Size Range	1 IPS
Conductor - AL Tube Std Size	1 IPS
Number Of Conductors	1
Conductor - Connection Combination	Tube to Flat
Conductor Type	• AL Tube Std-Size • CU Tube Std-Size
Conductor - Copper Tube Std Size Range	1 IPS
Conductor - Copper Tube Std Size	1 IPS

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Pad Configuration	4 holes
Physical Attribute - Pad Alignment	Offset

Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - G inch	1.50 in
Dimension - Pad Width inch	3.00 in
Package Height	0.000 in
Dimension - Height mm	85.9 mm
Dimension - Height inch	3.38 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	171 mm
Dimension - Width mm	78 mm
Dimension - Width inch	3.06 in
Dimension - B Length inch	3.50 in
Dimension - D inch	3.00 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	6.75 in

General

Material - Hardware	Aluminum
One Wrench Installation	Y
Plated	N
Clamping Element Design	Body and Cap
UPC	621945137875
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	621945137875
UPC 14 Digit GTIN	00621945137875

Logistics

Minimum Pack Quantity	1
Pallet Quantity	750
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)