




NA15A4NGS, Substation - Aluminum Bolted Terminal

By Burndy

Catalog # [NA15A4NGS](#)

Substation Connectors



Features

- Type NA-A Aluminum Terminals for Tube to Pad
- Properly proportioned to minimize conductor corrosion due to galvanic action
- When properly used, this item does not require use of bimetallic plates, contact Burndy Technical Support for recommendations
- One-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Tube Std Size Range	1 IPS
Conductor - AL Tube Std Size	1 IPS
Number Of Conductors	1
Conductor - Connection Combination	Tube to Flat
Conductor Type	• AL Tube Std-Size • CU Tube Std-Size
Conductor - Copper Tube Std Size Range	1 IPS IPS
Conductor - Copper Tube Std Size	1 IPS IPS

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Pad Configuration	3 x 3 - 4 holes
Physical Attribute - Pad Alignment	Offset

Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - G inch	1.50 in
Dimension - Pad Width inch	3.00 in
Dimension - Height mm	85.9 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	3.38 in
Dimension - Width mm	78 mm
Dimension - Width inch	3.06 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - L Length Overall mm	171 mm
Dimension - B Length inch	3.50 in
Dimension - D inch	3.00 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	6.75 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

Plated	N
Material - Hardware	Aluminum
One Wrench Installation	Y
Clamping Element Design	Body and Cap
UPC	781810480700
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810480700
UPC 14 Digit GTIN	00781810480700

Logistics

Minimum Pack Quantity	4
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)



A Hubbell brand