



K2A44U2N, AL Universal Terminal, 2-Conductor, 2-Hole

By Burndy
Catalog # [K2A44U2N](#)

2-Conductor, 2-Hole, 1/2" Stud, 1.75" Spacing, 500-1000 kcmil, Tin Plated



Features

- Dual rated panelboard lugs
- Constructed from high strength, extruded aluminum alloy
- Electro tin-plated to provide low contact resistance

Application

Terminal

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	NC
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil • 715 kcmil • 750 kcmil • 795 kcmil • 800 kcmil • 874 kcmil • 900 kcmil • 954 kcmil • 1000 kcmil
Conductor - AL Str Size Range	500 -1000 Kcmil
Conductor - Copper Str Size	• 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil

Conductor Size	• 800 kcmil
Number Of Conductors	• 850 kcmil
Conductor Type	• 900 kcmil
	• 1000 kcmil
Conductor - Copper Str Size Range	500-1000 KCMIL
	2
	• AL C Str-Size
	• CU C Str-Size
	500 -1000 Kcmil

Configuration

Physical Attribute - Number of Holes	2
Connector Type	Parallel Set-Screw

Dimensions

Dimension - Pad Width inch	3.21 in
Package Height	2.300 in
Dimension - Height mm	49.5 mm
Dimension - Height inch	1.95 in
Dimension - Height fraction	2 in
Package Weight	3.630 lb.
Package Length	10.000 in
Package Width	5.600 in
Dimension - L Length Overall mm	121 mm
Dimension - Width fraction	3-19/100 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Screw Size inch	3/8
Dimension - Stud Size inch	1/2 in
Dimension - Bolt Hole Size inch	0.50 in
Dimension - Bolt Size fraction	1/2
Dimension - Width mm	81 mm
Dimension - Width inch	3.21 in
Dimension - D inch	3.03 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	4.75 in

Force Related

Installation Torque Recommended in-lb	375 LBS/in
---------------------------------------	------------

General

Material - Hardware	Aluminum
Physical Attribute - Screw Type	Slot
Plated	N
Sub Brand	UNIVERSAL TERM
UPC	781810600450
Type	Bolted Lugs & Terminals
Material	Aluminum
Plating Type	Tin plated
UPC 12 Digit	781810600450
Hardware Type	3/8 UNC Slotted Set Screw
UPC 14 Digit GTIN	00781810600450

Logistics

Minimum Pack Quantity	1
Pallet Quantity	36
Carton Quantity	36

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand