




NA20A44NGS, Substation - Aluminum Bolted Terminal

By Burndy
Catalog # [NA20A44NGS](#)

Substation Connectors



Features

- Type NA-A Aluminum Terminals for Tube to Pad
- Properly proportioned to minimize conductor corrosion due to galvanic action
- When properly used, this item does not require use of bimetallic plates, contact Burndy Technical Support for recommendations
- One-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Number Of Conductors	1
Conductor - Connection Combination	Tube to Flat
Conductor Type	• AL Tube Std-Size • CU Tube Std-Size

Configuration

Physical Attribute - Pad Configuration	4 x 4.25 - 4 holes
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - G inch	2.43 in
Dimension - Pad Width inch	4.00 in

Package Height	0.000 in
Dimension - Height mm	138.9 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	5.47 in
Package Weight	0.000 lb.
Dimension - Width mm	143 mm
Dimension - Width inch	5.62 in
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	217 mm
Dimension - B Length inch	5.00 in
Dimension - D inch	4.25 in
Dimension - N inch	1.12 in
Dimension - Length Overall inch	8.56 in

Force Related

Installation Torque Recommended in-lb	660 LBS/in
---------------------------------------	------------

General

Plated	N
Material - Hardware	Aluminum
One Wrench Installation	Y
Clamping Element Design	Body and Cap
UPC	781810351901
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810351901
UPC 14 Digit GTIN	00781810351901

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)