




K2C22B1TN, SERVIT POST Mech Connector, 2 Cables to Flat

By Burndy
Catalog # [K2C22B1TN](#)



2 Copper Cables to Flat, #10-#2 Solid, #10-#3 Stranded, 3/8" Stud, Tin Plated

Features

- SERVIT POST mechanical connector used to ground 1 or 2 cables to steel structures, fence posts, and transformers
- Also used to tap 1 or 2 cables from bus bar
- 1-Wrench installation

- 7 AWG
- 6 AWG
- 5 AWG
- 4 AWG
- 3 AWG

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Solid Size Range	10 AWG-2 AWG
Physical Attribute - Number of Conductors Accommodated Total	2
Conductor - Copper Str Size Range	10 AWG-3 AWG
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG

Dimensions

Dimension - Height mm	31.8 mm
Dimension - Height inch	1.25 in
Dimension - Body Width inch	0.62 in
Dimension - P inch	0.26 in
Dimension - L Length Overall mm	60 mm
Dimension - B Length inch	0.96 in
Dimension - Nut Width inch	0.75 in
Dimension - D inch	1.12 in
Dimension - Length Overall inch	2.38 in

Force Related

Stud Installation Torque inch pounds	280 LBS/in
--------------------------------------	------------

General

Plated	Y
Trade Name	SERVIT POST™
UPC	781810110621
Type	KC and K2C Series
Material	Bronze Alloy, Leaded
Plating Type	Tin Plated
UPC 12 Digit	781810110621
UPC 14 Digit GTIN	00781810110621

Logistics

Minimum Pack Quantity	1
Pallet Quantity	14850
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)