




K4A31U4N, AL Universal Terminal, 4-Conductor, 4-Hole

By Burndy
Catalog # [K4A31U4N](#)



4-Conductor, 4-Hole, 1/2" Stud, 1.75" Spacing, #6 AWG-350 kcmil, Tin Plated

Features

- Dual rated lugs
- Constructed from high strength aluminum alloy
- Electro tin plating proving low contact resistance

Application

For Aluminum and Copper Conductors

Specifications

Buy American Compliant	Yes
Buy America(n) Qualified	• Buy America Compliant (All status valid till December 2026) • Buy American Act Compliant (All status valid till December 2026) • BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	NC
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil
Conductor - AL Str Size Range	6 AWG (Str)-350 kcmil
Conductor - Copper Str Size	• 6 AWG • 5 AWG • 4 AWG • 3 AWG

- 2 AWG
- 1 AWG
- 1/0
- 2/0 AWG
- 3/0 AWG
- 4/0 AWG
- 250 kcmil
- 300 kcmil
- 350 kcmil

Conductor Size	6 AWG-350 KCMIL
Number Of Conductors	4
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	6 AWG (Str)-350 kcmil

Configuration

Physical Attribute - Number of Holes	4
Connector Type	Parallel Set-Screw

Dimensions

Dimension - Pad Width inch	4.72 in
Package Height	0.000 in
Dimension - Height mm	35.1 mm
Dimension - Height inch	1.38 in
Dimension - Height fraction	1.4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	115 mm
Dimension - Width fraction	5-1/25 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Stud Size inch	1/2 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Bolt Size fraction	1/2
Dimension - Width mm	128 mm
Dimension - Width inch	5.04 in
Dimension - D inch	3.00 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	4.50 in

Force Related

Installation Torque Recommended in-lb	275 LBS/in	UPC 12 Digit UPC 14 Digit GTIN	781810370421 00781810370421
General		Logistics	
Product Family	MECHANICAL	Minimum Pack Quantity	1
Material - Hardware	Aluminum	Pallet Quantity	576
Physical Attribute - Screw Type	Allen	Carton Quantity	24
Plated	Yes	Operational	
Sub Brand	UNIVERSAL TERM	Temperature Rating	194
Product Type	Terminal	Product Assets	
UPC	781810370421	Catalog [English]	
Type	Bolted Lugs & Terminals		
Material	Aluminum		
Plating Type	Tin		

