



KA25UG4, AL Set Screw Terminal, Dual Rated, 2-Hole

By Burndy
Catalog # [KA25UG4](#)

Aluminum Universal Terminal, 2-Hole, 1/2" Stud, 1.75" Spacing,
#6-2/0 AWG, Tin Plated



Features

- Dual rated panelboard lugs constructed from high strength extruded aluminum alloy , electro tin-plated to provide low contact resistance

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - AL Str Size Range	6 AWG-2/0 AWG
Conductor Type	• CU C Str-Size • AL C Str-Size
Conductor - Copper Str Size Range	6 AWG-2/0 AWG
Conductor - Copper Str Size	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	2

Dimensions

Dimension - Pad Width inch	1.00 in
Package Height	0.000 in
Dimension - Height mm	30.2 mm
Length	4.25 in
Dimension - Height inch	1.19 in
Dimension - Height fraction	1-9/50 in
Dimension - B Length fraction	1 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	108 mm
Dimension - B Length inch	1.00 in
Height	1.19 in
Width	1 in
Dimension - D inch	3.25 in
Dimension - N inch	0.63 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	4.25 in
Dimensions	4.25 in x 1 in x 1.19 in

General

Physical Attribute - Screw Type	Allen
Plated	Y
Material - Hardware	Aluminum
UPC	781810363416
Type	Bolted Lugs & Terminals
Material	Aluminum
Plating Type	Tin - Electro Plated
Hardware Type	7/16 Hex/Socket SetScrew
UPC 14 Digit GTIN	00781810363416

Logistics

Minimum Pack Quantity	500
Pallet Quantity	72
Carton Quantity	72

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand