




NA22A4NU, Substation - Aluminum Bolted Terminal

By Burndy

Catalog # [NA22A4NU](#)

Substation Connectors



Features

- Type NA-A Aluminum Terminals for Tube to Pad
- Properly proportioned to minimize conductor corrosion due to galvanic action
- When properly used, this item does not require use of bimetallic plates, contact Burndy Technical Support for recommendations
- One-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Tube Std Size Range	4 IPS
Conductor - AL Tube Std Size	4 IPS
Number Of Conductors	1
Conductor - Connection Combination	Tube to Flat
Conductor Type	• AL Tube Std-Size • CU Tube Std-Size
Conductor - Copper Tube Std Size Range	4 IPS IPS
Conductor - Copper Tube Std Size	4 IPS IPS

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Pad Configuration	5.26 x 3 - 0 holes
Physical Attribute - Pad Alignment	Offset

Connector Type

Terminal

Dimensions

Dimension - G inch	2.94 in
Dimension - Pad Width inch	5.25 in
Dimension - Height mm	158 mm
Dimension - Height inch	6.22 in
Dimension - Width mm	168 mm
Dimension - Width inch	6.62 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - L Length Overall mm	236 mm
Dimension - B Length inch	6.00 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	9.31 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

Plated	N
Material - Hardware	Aluminum
One Wrench Installation	Y
Clamping Element Design	Body and Cap
UPC	781810119396
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810119396
UPC 14 Digit GTIN	00781810119396

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)