




KA36U2N, AL Universal, 2-Hole, Dual Rated

By Burndy
Catalog # [KA36U2N](#)

Aluminum Universal Terminal, 2 Hole, 2 AWG (Str)-600 kcmil, 1/2" Stud, 1.75" Stud Hole Spacing, 1 Screw, Al/Cu Rated, Tin Plated



Features

- Dual Rated Panelboard Lugs
- High strength extruded aluminum alloy
- Electro tin-plated for low contact resistance
- Rated to 35kV

Application

For Aluminum and Copper Conductors

Specifications

Buy American Compliant	Yes
Buy America(n) Qualified	• Buy America Compliant (All status valid till December 2026) • Buy American Act Compliant (All status valid till December 2026) • BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil
-------------------------	---

Conductor - AL Str Size Range	2 AWG-600 kcmil
Conductor - Copper Str Size	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil
Conductor Size	2 AWG-600 KCMIL
Conductor - Copper Solid Size	• 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Number Of Conductors	1
Conductor - Copper Solid Size Range	1 AWG-4/0 AWG
Conductor Type	• AL C Str-Size • CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	2 AWG-600 kcmil

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.52 in
Package Height	2.100 in
Dimension - Height mm	39.9 mm
Dimension - Height inch	1.57 in
Dimension - Height fraction	1.5714285714285714 in
Package Weight	1.430 lb.
Package Length	6.000 in
Package Width	6.450 in

Dimension - L Length Overall mm	119 mm
Dimension - Width fraction	1-1/2 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Stud Size inch	1/2
Dimension - Bolt Hole Size inch	0.50 in
Dimension - Bolt Size fraction	1/2
Dimension - Width mm	38 mm
Dimension - Width inch	1.50 in
Dimension - D inch	3.22 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	4.69 in

Force Related

Installation Torque Recommended	500 LBS/in
in-lb	

General

Product Family	MECHANICAL
Material - Hardware	Aluminum



A Hubbell brand

Physical Attribute - Screw Type	Allen
Plated	Yes
Sub Brand	UNIVERSAL TERM
Product Type	Terminal
UPC	781810370407
Type	Bolted Lugs & Terminals
Material	Aluminum
Plating Type	Tin
UPC 14 Digit GTIN	00781810370407

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1584
Carton Quantity	66

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)