


NA22ACG4, Substation - Aluminum Bolted Terminal

By Burndy
Catalog # [NA22ACG4](#)

Substation Connectors



Features

- Type NA-A Aluminum Terminals for Tube to Pad
- Properly proportioned to minimize conductor corrosion due to galvanic action
- When properly used, this item does not require use of bimetallic plates, contact Burndy Technical Support for recommendations
- One-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Tube Std Size Range	4 IPS
Conductor - AL Tube Std Size	4 IPS
Number Of Conductors	1
Conductor - Connection Combination	Tube to Flat
Conductor Type	• AL Tube Std-Size • CU Tube Std-Size
Conductor - Copper Tube Std Size Range	4 IPS IPS
Conductor - Copper Tube Std Size	4 IPS IPS

Configuration

Physical Attribute - Pad Alignment	Straight
Orientation	

Physical Attribute - Pad Alignment	Offset
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.50 in
Dimension - Height mm	158 mm
Dimension - Height inch	6.22 in
Dimension - Width mm	156 mm
Dimension - Width inch	6.14 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - L Length Overall mm	256 mm
Dimension - B Length inch	6.00 in
Dimension - D inch	3.75 in
Dimension - N inch	0.88 in
Dimension - Length Overall inch	10.06 in

General

Plated	N
Material - Hardware	Aluminum
One Wrench Installation	Y
Clamping Element Design	Body and Cap
UPC	621945238428
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	621945238428
UPC 14 Digit GTIN	00621945238428

Logistics

Minimum Pack Quantity	2
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)