




KA40U2N, AL Universal Terminal, 2-Hole, Dual Rated

By Burndy
Catalog # [KA40U2N](#)

Aluminum Universal Terminal, 2 Hole, 300-800 kcmil, 1/2" Stud, 1.75" Stud Hole Spacing, 1 Screw, Al/Cu Rated, Tin Plated



Features

- Dual Rated Panelboard Lugs
- High strength extruded aluminum alloy
- Electro tin-plated for low contact resistance
- Rated to 35kV

Application

For Aluminum and Copper Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil • 715 kcmil • 750 kcmil • 795 kcmil • 800 kcmil
Conductor - AL Str Size Range	300 kcmil-800 kcmil

Conductor - Copper Str Size	• 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil • 800 kcmil
Conductor Size	300-800 KCMIL
Number Of Conductors	1
Conductor Type	• CU C Str-Size • AL C Str-Size
Conductor - Copper Str Size Range	300 kcmil-800 kcmil

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.77 in
Package Height	0.000 in
Dimension - Height mm	49.5 mm
Dimension - Height inch	1.95 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	121 mm
Dimension - Width fraction	1-3/4 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Stud Size inch	1/2
Dimension - Bolt Hole Size inch	0.50 in
Dimension - Bolt Size fraction	1/2
Dimension - Width mm	44 mm
Dimension - Width inch	1.75 in
Dimension - D inch	3.03 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	4.75 in

Force Related

Installation Torque Recommended in-lb	500 LBS/in	Material Plating Type UPC 14 Digit GTIN	Aluminum Tin 00781810370452
General		Logistics	
Product Family	MECHANICAL	Minimum Pack Quantity	1
Material - Hardware	Aluminum	Pallet Quantity	2520
Physical Attribute - Screw Type	Allen	Carton Quantity	54
Plated	Yes		
Sub Brand	UNIVERSAL TERM		
Product Type	Terminal		
UPC	781810370452		
Type	Boiled Lugs & Terminals		



Product Assets
[Catalog \[English\]](#)