



KA4CG16, Copper Mechanical Terminal, 1-Hole

By Burndy
Catalog # [KA4CG16](#)

High Copper Alloy Terminal, #14 Solid - #4 Stranded Copper;
5/16" Stud

Features

- Compact, high copper alloy terminal for joining cable to equipment pads or terminal blocks

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Solid Size	• 14 • 13 • 12 • 11 • 10 • 9 • 8 • 7 • 6 • 5 • 4
Conductor - Copper Solid Size Range	14-4
Conductor Type	• CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	14-4
Conductor - Copper Str Size	• 14 • 12 • 10 • 9 • 8 • 7 • 6 • 5



• 4

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.54 in
Dimension - Height mm	19.6 mm
Dimension - Height inch	0.77 in
Dimension - Height fraction	67/87 in
Dimension - B Length fraction	8/17 in
Dimension - L Length Overall mm	28 mm
Dimension - B Length inch	0.47 in
Dimension - N inch	0.25 in
Dimension - Hole Size mm	8 mm
Dimension - Hole Size inch	0.32 in
Dimension - Length Overall inch	1.11 in

General

Physical Attribute - Screw Type	Slot
Plated	N
Material - Hardware	Steel
UPC	781810006269
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
Hardware Type	5/16 UNF Slotted SetScrew
UPC 14 Digit GTIN	00781810006269

Logistics

Minimum Pack Quantity	1
Pallet Quantity	59400
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)



A Hubbell brand