




Substation - Aluminum Bolted Terminal

By Burndy
Catalog # [NA34A4NCG2](#)

Substation Connectors

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Number Of Conductors	1
Conductor - Connection Combination	Cable to Flat
Conductor Type	• AL Tube Std-Size • CU Tube Std-Size

Configuration

Physical Attribute - Pad Orientation	90 Degree
Physical Attribute - Pad Configuration	4 holes
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - G inch	4.81 in
Dimension - Pad Width inch	4.38 in
Package Height	0.000 in
Dimension - Height mm	162.1 mm
Dimension - Hole Size fraction	9/16

Dimension - Height inch	6.38 in
Package Weight	0.000 lb.
Dimension - Width mm	65 mm
Dimension - Width inch	2.56 in
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	86 mm
Dimension - B Length inch	3.00 in
Dimension - D inch	3.50 in
Dimension - N inch	0.84 in
Dimension - Length Overall inch	3.38 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

Plated	N
Material - Hardware	Aluminum
One Wrench Installation	Y
Clamping Element Design	Body and Cap
UPC	621945109353
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	621945109353
UPC 14 Digit GTIN	00621945109353

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)