



Substation - Copper Terminal

By Burndy
Catalog # [NAH402N](#)

Cast Copper alloy terminal, 2/0 Sol-800 kcmil, 5.88 in Length,
Cable to Pad



Application

Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	2/0 AWG 3/0 AWG 4/0 AWG 250 kcmil 300 kcmil 350 kcmil 400 kcmil 450 kcmil 500 kcmil 550 kcmil 600 kcmil 700 kcmil 750 kcmil 800 kcmil
Conductor - Copper Solid Size	3/0 AWG 4/0 AWG
Number Of Conductors	1
Conductor - Connection	Cable to Flat
Combination	
Conductor - Copper Solid Size Range	3/0 AWG-4/0 AWG
Conductor Type	- CU C Str-Size - CU C Solid-Size
Conductor - Copper Str Size Range	2/0 AWG-800 kcmil

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Pad Configuration	2 x 3 - 2 holes

Physical Attribute - Pad Alignment	Offset
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Size inch	2 x 3
Dimension - Pad Width inch	2.00 in
Package Height	0.000 in
Dimension - Height mm	66.5 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	2.62 in
Dimension - Height fraction	2-31/50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	149 mm
Dimension - Hole Size inch	0.56 in
Dimension - B Length fraction	2-31/50 in
Dimension - Width mm	71 mm
Dimension - Width inch	2.81 in
Dimension - B Length inch	2.62 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	5.88 in

General

Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Plated	N
Clamping Element Design	Body and Cap
UPC	781810002896
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810002896
UPC 14 Digit GTIN	00781810002896

Logistics

Pallet Quantity	540
Carton Quantity	5



A Hubbell brand