




Substation - Copper Terminal

By Burndy

Catalog # [NAH442N90](#)

Substation Connectors



Application

Substation

Physical Attribute - Number of Holes2

Connector TypeTerminal

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Number Of Conductors	1
Conductor - Connection Combination	Cable to Flat
Conductor Type	- CU C Str-Size - CU C Solid-Size
Conductor - Copper Str Size Range	4/0 AWG-1000 kcmil
Conductor - Copper Str Size	4/0 AWG 250 kcmil 300 kcmil 350 kcmil 400 kcmil 450 kcmil 500 kcmil 550 kcmil 600 kcmil 700 kcmil 750 kcmil 800 kcmil 850 kcmil 900 kcmil 1000 kcmil

Configuration

Physical Attribute - Pad Orientation	90 Degree
Physical Attribute - Pad Configuration	2 x 3 - 2 holes
Physical Attribute - Pad Alignment	Offset

Dimensions

Dimension - Pad Size inch	2 x 3
Dimension - Pad Width inch	2.00 in
Package Height	0.000 in
Dimension - Height mm	143 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	5.63 in
Package Weight	0.000 lb.
Dimension - Width mm	73 mm
Dimension - Width inch	2.88 in
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	143 mm
Dimension - B Length inch	2.88 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	5.63 in

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Clamping Element Design	Body and Cap
UPC	781810064672
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810064672
UPC 14 Digit GTIN	00781810064672

Logistics

Pallet Quantity	1
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)

