



KAUKIT4, AL Alloy Transformer Lug Kit, Supplied w/ Hardware

By Burndy
Catalog # [KAUKIT4](#)

Transformer Lug Kit, 300-800 kcmil Class B&C, 300-750 kcmil Class G,H,I,K, DLO, Supplied with Hardware



Features

- UL Listed, CSA Certified, AL9CU dual rated set screw terminals to ensure the transformer feeders and taps are terminated properly
- Plated steel cap screws and hex nuts with captive conical washers or individual Belleville washers
- Terminal to bus connections made using proper hardware resulting in true torque to pressure performance compensates for dissimilar metal expansion and contraction
- Hardware packed in plastic bag to prevent lost hardware prior to installation
- Larger 800 kcmil lugs (KAUKIT3 and KAUKIT4 only) accommodates common 750 kcmil tap conductors in larger transformers

- 477 kcmil
- 500 kcmil
- 550 kcmil
- 556 kcmil
- 600 kcmil
- 636 kcmil
- 650 kcmil
- 700 kcmil
- 715 kcmil
- 750 kcmil
- 795 kcmil
- 800 kcmil

Application

used to provide low contact resistance

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Listed Direct	No
Burial	
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil
-------------------------	---

Configuration

Connector Type	Lug/Hardware Kit
----------------	------------------

Dimensions

Dimension - Height mm	0 mm
-----------------------	------

General

Sub Brand	UNIVERSAL TERM
UPC	781810600146
Type	Bolted Lugs & Terminals
Material	Aluminum
UPC 14 Digit GTIN	00781810600146

Logistics

Minimum Pack Quantity	1
Package Contents	• (15) K2A40U • (7) 1/2-13 x 2 in, (4) 1/2-13 x 2-1/2 in Hex Head Bolts • (11) 1/2-13 Hex Head Nuts • (22) 1/2 in Flat Washers • (11) 1/2 in Belleville Washers
Pallet Quantity	144
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)