



NAR36A2N, 2-Hole Substation Al/Cu Cable to Flat, 336.4-477 kcmil ACSR

By Burndy
Catalog # [NAR36A2N](#)

Terminal, 350 - 600 Kcmil Al/Cu 336.4 - 477 Kcmil ACSR, 2 Pad holes, 6-5/8 in Length, Cable to Flat

Features

- Aluminum alloy terminal for joining a wide range of copper or aluminum cable to copper or aluminum pad
- Properly proportioned to minimize conductor corrosion due to galvanic action
- Pad drilling conforms to NEMA standards
- 1-wrench installation

Application

Substation

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil
Conductor - AL Str Size Range	350 kcmil-600 kcmil
Conductor - ACSR Str Size	• 336.4 (30/7) Oriole kcmil • 397.5 (18/1) Chickadee kcmil • 397.5 (24/7) Brant kcmil • 397.5 (26/7) Ibis kcmil • 397.5 (30/7) Larkspur kcmil • 477.0 (18/1) Pelican kcmil • 477.0 (24/7) Flicker kcmil • 477.0 (26/7) Hawk kcmil • 477. (30/7) Hen kcmil
Conductor - ACSR Str Size Range	336.4 (30/7) Oriole kcmil-477. (30/7) Hen kcmil
Number Of Conductors	1



Conductor - Connection Combination	Cable to Flat
Conductor Type	• AL C Str-Size • ACSR C Str-Size

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Pad	1.69 x 3 - 2 holes
Configuration	
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.69 in
Package Height	4.63 in
Dimension - Height mm	71.4 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	2.81 in
Dimension - Height fraction	2-7/8 in
Package Weight	9.68 lb.
Package Length	12.63 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	6.38 in
Dimension - L Length Overall mm	168 mm
Dimension - Thread Size	1/2
Dimension - Bolt Size fraction	1/2
Dimension - Width mm	70 mm
Dimension - Width inch	2.75 in
Dimension - B Length inch	3.25 in
Dimension - D inch	3.00 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	6.63 in

Force Related

Installation Torque Recommended in-lb	300 LBS/in
---------------------------------------	------------

General

Product Family	Substation>Aluminum >Terminals (NON EHV)>Cable to Flat>Single Conductor
Material - Hardware	Aluminum

One Wrench Installation	Y
Plated	No
Sub Brand	SUBSTATION CONNECTOR
Clamping Element Design	Body And Cap
Product Type	Mechanical
UPC	781810003848
Type	NAR-A
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810003848

UPC 14 Digit GTIN00781810003848

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1080
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)



A Hubbell brand