

Substation - Connector

By Burndy
Catalog # [NBC15A2N](#)

Substation Connectors



Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No
Conductor	
Conductor - AL Tube Std Size Range	1 IPS
Conductor - AL Tube Std Size	1 IPS
Conductor - Connection Combination	Tube to Flat
Conductor Type	AL Tube Std-Size

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Pad Configuration	2 x 3.25 - 2 holes
Physical Attribute - Pad Alignment	Centered
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Holes	2
Connector Type	T-Connector

Dimensions

Dimension - Pin Diameter inch	1.32 in
Dimension - Pin Diameter fraction	1-8/25 in
Dimension - Pad Size inch	2 x 3.25

Dimension - Pad Width inch	2.00 in
Package Height	0.000 in
Dimension - Height mm	76.2 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	3.00 in
Dimension - B Length fraction	3-1/2 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	173 mm
Dimension - B Length inch	3.50 in
Dimension - D inch	3.25 in
Dimension - N inch	0.62 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	6.81 in

Force Related

Installation Torque Recommended in-lb	300 LBS/in
---------------------------------------	------------

General

Plated	N
Material - Hardware	Aluminum
One Wrench Installation	Y
UPC	781810066263
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810066263
UPC 14 Digit GTIN	00781810066263

Logistics

Pallet Quantity	648
Carton Quantity	2

Product Assets

[Catalog \[English\]](#)