



KC22B2TN, SERVIT POST Mech Conn, Cable to Flat, Tin Plated

By Burndy
Catalog # [KC22B2TN](#)

Mechanical SERVIT POST™ Connector; Cable to Flat



Features

- SERVIT POST tin-plated mechanical connector used to ground 1 or 2 cables to steel structures, fence posts, and transformers
- Also used to tap 1 or 2 cables from bus bar
- 1-Wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	8 AWG 7 AWG 6 AWG 5 AWG 4 AWG 3 AWG 2 AWG
Conductor - Copper Solid Size Range	2 AWG-10 AWG
Physical Attribute - Number of Conductors Accommodated Total	1

Conductor - Copper Str Size Range	3 AWG-10 AWG
-----------------------------------	--------------

Dimensions

Dimension - Height mm	25.4 mm
Dimension - Height inch	1.00 in
Dimension - Width mm	22 mm
Dimension - Width inch	0.88 in
Dimension - P inch	0.27 in
Dimension - L Length Overall mm	38 mm
Dimension - B Length inch	0.41 in
Dimension - Cross Flats inch	0.62 in
Dimension - D inch	0.50 in
Dimension - Length Overall inch	1.50 in

General

Plated	N
Trade Name	SERVIT POST™
UPC	781810523681
Type	KC and K2C Series
Material	Bronze, Leaded, Commercial
Plating Type	Tin Plated
UPC 12 Digit	781810523681
UPC 14 Digit GTIN	00781810523681

Logistics

Minimum Pack Quantity	100
Pallet Quantity	5800
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)