



Substation - Connector

By Burndy
Catalog # [NBC17A34N](#)

Substation Connectors



Application

Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Tube Std Size Range	1 1/2 IPS
Conductor - AL Tube Std Size	1 1/2 IPS
Conductor - Connection Combination	Tube to Flat
Conductor Type	AL Tube Std-Size

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Pad Configuration	3 x 3.25 - 4 holes
Physical Attribute - Pad Alignment	Centered
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Holes	4
Connector Type	T-Connector

Dimensions

Dimension - Pin Diameter inch	1.90 in
Dimension - Pin Diameter fraction	1-9/10 in
Dimension - Pad Size inch	3 x 3.25

Dimension - Pad Width inch	3.00 in
Package Height	0.000 in
Dimension - Height mm	88.9 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	3.50 in
Dimension - Height fraction	3-1/2 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	188 mm
Dimension - Hole Size inch	0.56 in
Dimension - B Length inch	4.00 in
Dimension - D inch	3.25 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	7.39 in

Force Related

Installation Torque	300 LBS/in
Recommended in-lb	

General

Material - Hardware	Aluminum
One Wrench Installation	Y
Plated	N
UPC	781810234525
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810234525
UPC 14 Digit GTIN	00781810234525

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)