



KC25TN, SERVIT POST Mech Conn, Cable to Flat, Tin Plated

By Burndy
Catalog # [KC25TN](#)

SERVIT POST™ Connector; Cable to Flat, Accommodates #2-1/0 Str or #2-2/0 Solid Copper, 1/2" Stud, Tin Plated

Features

- SERVIT POST tin-plated mechanical connector used to ground 1 or 2 cables to steel structures, fence posts, and transformers
- Also used to tap 1 or 2 cables from bus bar
- 1-Wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - Copper Solid Size Range	2 AWG-2/0 AWG
Physical Attribute - Number of Conductors Accommodated Total	1
Conductor - Copper Str Size Range	2 AWG-1/0
Conductor - Copper Str Size	• 2 AWG • 1 AWG • 1/0

Dimensions

Package Height	0.000 in
Dimension - Height mm	30.2 mm
Dimension - Height inch	1.19 in
Dimension - Body Width inch	0.75 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	0.39 in
Dimension - L Length Overall mm	49 mm
Dimension - B Length inch	0.53 in
Dimension - Nut Width inch	0.93 in
Dimension - D inch	0.75 in
Dimension - Length Overall inch	1.94 in

Force Related

Stud Installation Torque inch pounds	480 LBS/in
--------------------------------------	------------

General

Plated	N
Trade Name	SERVIT POST™
UPC	781810141915
Type	KC and K2C Series
Material	Bronze, Leaded, Commercial
Plating Type	Tin Plated
UPC 12 Digit	781810141915
UPC 14 Digit GTIN	00781810141915

Logistics

Pallet Quantity	9900
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)