



KC34J12T13, Mech Transformer Conn, 3/0 - 500 kcmil Copper

By Burndy
Catalog # [KC34J12T13](#)

Mechanical Transformer Connector

Features

- SERVIT POST tin-plated mechanical connector used to ground 1 or 2 cables to steel structures, fence posts, and transformers
- Also used to tap 1 or 2 cables from bus bar
- 1-Wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Physical Attribute - Number of Conductors Accommodated Total	1
Conductor - Copper Str Size Range	3/0 AWG-500 Kcmil
Conductor - Copper Str Size	1 AWG 1/0 2/0 AWG 3/0 AWG 4/0 AWG 250 kcmil 300 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	60.5 mm
Dimension - Bolt Size fraction	1/2
Dimension - Body Width inch	1.62 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	0.85 in
Dimension - Nut Width inch	2.00 in
Dimension - Threads per inch	13
Dimension - Length Overall inch	3.62 in

Force Related

Installation Torque	1050 LBS/in
Recommended in-lb	
Stud Installation Torque inch pounds	1050 LBS/in

General

Plated	N
Trade Name	SERVIT POST™
UPC	781810135280
Type	KC and K2C Series
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810135280
UPC 14 Digit GTIN	00781810135280

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)