



NHNT2044, Substation Copper T Connector, 90 Degrees

By Burndy
Catalog # [NHNT2044](#)

Substation Connectors

Features

- High copper alloy reversible T-Connector for joining a wide range of run pipe and tap cables
- Connector is designed for one-wrench installation

Application


Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Tube to Cable
Conductor Type	• CU Tube Std-Run • CU C Str-Run • CU C Solid-Run • CU C Str-Tap • CU C Solid-Tap
Conductor - Copper Str Tap Range	4/0 AWG-1000 kcmil
Conductor - Copper Str Tap	• 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil • 800 kcmil • 850 kcmil • 900 kcmil • 1000 kcmil
Conductor - Copper Tube Std Run Range	3 IPS



Conductor - Copper Tube Std Run 3 IPS

Configuration

Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Number of Run Conductors	1
Connector Type	T-Connector

Dimensions

Dimension - Height mm	108.2 mm
Dimension - Height inch	4.26 in
Dimension - Height fraction	5-3/4 in
Dimension - B Length fraction	2-69/100 in
Dimension - Width mm	74 mm
Dimension - Width inch	2.90 in
Dimension - L Length Overall mm	227 mm
Dimension - B Length inch	2.69 in
Dimension - Width fraction	2-9/10 in
Dimension - Length BB inch	5.75 in
Dimension - Length Overall inch	8.95 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
UPC	781810143094
Type	Tube to Cable Couplers
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810143094
UPC 14 Digit GTIN	00781810143094

Logistics

Minimum Pack Quantity	2
Pallet Quantity	1
Carton Quantity	1



A Hubbell brand