

KPA34UNPL, Pressure Bar Cu Lug, 1-Hole, Unplated

By Burndy

Catalog # [KPA34UNPL](#)

Mechanical Pressure Bar Style Copper Lug, 1-Hole, 1/2" Stud, 4/0 AWG - 500 kcmil, Unplated



Features

- High copper alloy terminal (unplated) for joining a wide range of cable to equipment pads or terminal blocks
- Tongue and body are 1-piece design, pressure bar equalizes pressure over the conductor and prevents the screw from cutting into the cable

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil
Conductor Size	4/0 AWG-500 KCMIL
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	4/0 AWG-500 kcmil

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Pressure Bar

Dimensions

Dimension - Pad Width inch	1.38 in
Package Height	0.000 in
Dimension - Height mm	62 mm
Dimension - Height inch	2.44 in
Dimension - Height fraction	2-7/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	84 mm
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.54 in
Dimension - Stud Size inch	1/2
Dimension - Bolt Size fraction	1/2
Dimension - D inch	1.38 in
Dimension - N inch	0.75 in
Dimension - Length Overall inch	3.32 in

Force Related

Installation Torque	375
Recommended in-lb	

General

Trade Name	SCRULUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810172742
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810172742

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2664
Carton Quantity	18

Product Assets

[Catalog \[English\]](#)