



Substation - Aluminum Bolted T Connector

By Burndy
Catalog # [NNT14A14A](#)

Substation Connectors



Features

- Type NNT Aluminum T-Connectors for Aluminum and Copper Tube to Tube
- Properly proportioned to permit use on copper-aluminum conductor combinations
- Captured hex head bolts permit one-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Tube Std Run Range	3/4 IPS
Conductor - AL Tube Std Run	3/4 IPS
Conductor - Connection Combination	Tube to Tube
Conductor - AL Tube Std Tap Range	3/4 IPS
Conductor - AL Tube Std Tap	3/4 IPS
Conductor Type	• AL Tube Std-Run • AL Tube Std-Tap

Configuration

Physical Attribute - Pad Orientation	90 Degree
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Number of Run Conductors	1

Connector Type	T-Connector
----------------	-------------

Dimensions

Package Height	0.000 in
Dimension - Height mm	79.5 mm
Dimension - Height inch	3.13 in
Package Weight	0.000 lb.
Dimension - Width mm	71 mm
Dimension - Width inch	2.81 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	160 mm
Dimension - B Length inch	3.25 in
Dimension - Length BB inch	3.25 in
Dimension - Length Overall inch	6.31 in

Force Related

Installation Torque Recommended in-lb	300 LBS/in
---------------------------------------	------------

General

Plated	N
Material - Hardware	Aluminum
One Wrench Installation	Y
UPC	781810078570
Type	Bolted Tees
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810078570
UPC 14 Digit GTIN	00781810078570

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)