


KPA4CTPG3, Mechanical Pressure Bar Style Copper Lug, 1-Hole

By Burndy

Catalog # [KPA4CTPG3](#)



Copper Alloy SCRULUG with Pressure Bar, 1-Hole, 1/4" Stud, #14-
#6 Tin Plated

Features

- High copper alloy terminal (tin-plated) for joining a wide range of cable to equipment pads or terminal blocks
- Tongue and body are 1-piece design, pressure bar equalizes pressure over the conductor and prevents the screw from cutting into the cable

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size Range	14 AWG-4 AWG
Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.50 in
Package Height	0.000 in
Dimension - Height mm	25.4 mm
Dimension - Height inch	1.00 in
Dimension - Height fraction	1 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	33 mm
Dimension - D inch	0.71 in
Dimension - N inch	0.33 in
Dimension - Hole Size mm	7.1 mm
Dimension - Hole Size inch	0.28 in
Dimension - Length Overall inch	1.28 in

Force Related

Installation Torque Recommended in-lb	45 LBS/in
---------------------------------------	-----------

General

Physical Attribute - Screw Type Plated	Slot Y
Trade Name	SCRULUG™
UPC	781810079867
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810079867

Logistics

Minimum Pack Quantity	1
Pallet Quantity	39600
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)