




KS90, Split Bolt Connector, Run/Tap: #12-10 AWG Str

By Burndy
Catalog # [KS90](#)

Copper Split Bolt, Cu: 12-10 AWG (Str) (Run & Tap)



Features

- UL467 Listed for Direct Burial applications in earth or concrete
- Compact, high-strength, copper alloy with free-running threads and easy to grip wrench flats
- Highly resistant to cracking and corrosion

Application

For Direct Burial Cables

Specifications

Certification - UL Recognized	No
Buy American Compliant	Yes
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	• Buy America Compliant (All status valid till December 2026) • Buy American Act Compliant (All status valid till December 2026) • BABA Compliant (All status valid till December 2026)
Industry Standard(s)	• UL 486A • UL486B
Certification - ETL	No
Standards - Industry Standards Met	• UL 486A • UL486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	12 STR. 10 STR.
Conductor - Copper Str Run	• 12 AWG • 10 AWG
Conductor - Copper Solid Run Range	10 AWG-12 AWG
Conductor - Copper Solid Run	8 AWG
Conductor - Copper Solid Tap	16 AWG-10 AWG

Conductor - Copper Solid Tap	8 AWG
Conductor - CopperWeld Solid Tap Range	#10
Conductor - CopperWeld Solid Tap	#10
Conductor - CopperWeld Solid Run Range	#10
Conductor - CopperWeld Solid Run	#10
Conductor Type	• CU C Solid-Run • CU C Str-Run • CU Weld C Solid-Run • CU Weld C Str-Run • CU C Str-Tap • CU Weld C Solid-Tap • CU Weld C Str-Tap • CU C Solid-Tap
Conductor - Copper Str Tap Range	16 STR.
Conductor - Copper Str Tap	• 16 AWG • 14 AWG • 12 AWG • 10 AWG

Configuration

Connector Type	Split Bolt
----------------	------------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	22 mm
Width	0.38 in
Dimension - Width fraction	19/50 in
Dimension - B Length fraction	9/20 in
Dimension - Width mm	10 mm
Dimension - Width inch	0.38 in
Dimension - B Length inch	.45 in
Dimension - Cross Flats inch	.50 in
Dimension - Length Overall inch	0.85

Force Related

Installation Torque	80 in	UPC 12 Digit	781810015254
Recommended in-lb		UPC 14 Digit GTIN	00781810015254
General		Logistics	
Trade Name	SERVIT®	Minimum Pack Quantity	1
Plated	N	Pallet Quantity	99000
Sub Brand	SERVIT	Carton Quantity	100
UPC	781810015254	Product Assets	
Type	KS	Catalog [English]	
Material	Copper		
Plating Type	Unplated		



A Hubbell brand