



KVS31AG12, 2-piece OKLIP Service Connector for heavy duty applications, AL alloy

By Burndy
Catalog # [KVS31AG12](#)

Cast Al Alloy Mechanical OKLIP, 250 - 350 kcmil Cu/AAC, 4/0 AWG - 336.4 kcmil Al/ACSR(Run), #6 Str. - 350 kcmil Cu/AAC, #6 AWG - 336.4 kcmil Al/ACSR(Tap)

Features

- High conductivity, non-copper bearing aluminum alloy connector with thick spacer and aluminum hardware
- Recommended for heavy duty dissimilar metal applications
- Spacer separates conductors and provides long contact length
- Longer peened bolt permits swivel action for easier installation
- Neoprene ring prevents loss of shorter bolt

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• AL C Str-Run • CU C Str-Run • ACSR C Cmpt-Run • AAAC C 5005-Run • AAAC C 6201-Run • AL C Str-Tap • CU C Str-Tap
----------------	---



- ACSR C Cmpt-Tap
- AAAC C 5005-Tap
- AAAC C 6201-Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	N
Trade Name	OKLIP™
UPC	781810096765
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810096765
UPC 14 Digit GTIN	00781810096765

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5040
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)