



KVS44, 2-piece OKLIP Service Connector for heavy duty applications

By Burndy
Catalog # [KVS44](#)

Compact 2-piece, high strength, copper alloy with neoprene rings

Features

- Compact, 2-piece, high strength, high copper alloy, recommended for heavy duty connections
- Neoprene rings hold silicon bronze bolts in place during installation
- Installed with ordinary wrench

Application

For Copper And Copperweld, Heavy Duty Connections

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL486C
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL486C
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	500 kcmil- 1000 kcmil
Conductor Type	• CU C Str-Run • CU C Str-Tap • CU Weld C Solid-Run • CU Weld C Solid-Tap
Conductor - Copper Str Tap Range	3/0 str.- 1000 kcmil



Dimensions

Package Height	0.000 in
Dimension - Height mm	94.24 mm
Dimension - Height inch	3.71 in
Package Weight	0.000 lb.
Dimension - Width inch	3.03 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - Stud Size inch	5/8 in

Force Related

Installation Torque	500 LBS/in
Recommended in-lb	

General

Plated	N
Trade Name	OKLIP™
Sub Brand	OKLIP
UPC	781810064603
Type	KVS
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810064603
UPC 14 Digit GTIN	00781810064603

Logistics

Pallet Quantity	672
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)