



KVSU28, Mechanical Connector with Spacer Bar

By Burndy

Catalog # [KVSU28](#)

Tin plated copper alloy with tin plated hardware; spacer bar to separate dissimilar conductors

Features

- Compact, tin-plated high strength copper alloy connector with spacer and tin-plated silicon bronze hardware
- Recommended for heavy duty connections
- Spacer separates dissimilar conductors and provides long contact length
- Neoprene ring prevents loss of shorter bolt during installation
- Longer peened bolt permits swivel action for easier installation
- CSA Listed for Copper

Application

For All Combinations Of Copper, Aluminum, ACSR, AAAC And 5005

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor - Galvanized Steel Str Tap Range	5/32 in- 1/2 in
Conductor - Galvanized Steel Str Run Range	3/8 in- 1/2 in
Conductor - AL Str Run Range	1/0 str. - 4/0 str.
Conductor - AL Str Tap Range	6 str.- 4/0 str.
Conductor - ACSR Str Run Range	1/0 ACSR - 4/0 ACSR
Conductor - ACSR Str Tap Range	6 ACSR - 4/0 ACSR
Conductor - Copper Str Run Range	1/0 str. - 4/0 str.
Conductor - Copper Solid Run Range	2/0 AWG-4/0 AWG
Conductor - Copper Solid Run	• 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Tap Range	2/0 AWG-4/0 AWG
Conductor - Copper Solid Tap	• 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - CopperWeld Solid Tap Range	6 sol.- 4/0 sol.



Conductor - CopperWeld Solid Run Range 2/0 sol.- 4/0 sol.

Conductor Type

- AL C Str-Run
- AL C Str-Tap
- CU C Str-Run
- CU C Str-Tap
- AAAC C 5005-Run
- AAAC C 5005-Tap
- AAAC C 6201-Run
- AAAC C 6201-Tap
- ACSR C Str-Run
- ACSR C Str-Tap
- CU C Solid-Run
- CU C Solid-Tap
- GAL Steel C Str-Run
- GAL Steel C Str-Tap
- Cu Weld Sol.- Run
- Cu Weld Sol.- Tap

Conductor - Copper Str Tap Range 6 str.- 4/0 str.

Dimensions

Package Height	0.000 in
Dimension - Height mm	63.50 mm
Dimension - Height inch	2.50 in
Dimension - Height fraction	2-3/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	29 mm
Dimension - Width fraction	1-3/4 in
Dimension - Stud Size inch	3/8 in
Dimension - Width mm	44 mm
Dimension - Width inch	1.67 in
Dimension - Length Overall inch	1.04 in

Force Related

Installation Torque Recommended 250 LBS/in in-lb

General

Product Family	Power Connectors>Split Bolts>KVSU
Trade Name	OKLIP™
Plated	Yes
Sub Brand	OKLIP
Product Type	Mechanical

UPC	781810081808
Type	KVS, Compact, Universal
Construction Material - Main	Copper alloy
Material	Copper
Plating Type	Tin
Finish Type	Tin-Plated
UPC 12 Digit	781810081808
UPC 14 Digit GTIN	00781810081808

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3000
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)

