



KVSW40, Mechanical Connector with Spacer Bar

By Burndy

Catalog # [KVSW40](#)

Mechanical Connector For CUWeld and Copper Supplied with a
CU alloy Spacer that separates run and tap conductors, Run:
400-800 Kcmil, Tap: 4/0 str. - 800 kcmil



Features

- Compact, 2-piece, high strength, high copper alloy, recommended for heavy duty connections
- High copper alloy spacer bar separates run and tap conductors
- Provides high contact pressure, confines conductor strands and assures vibration-proof connection
- Longer peened bolt permits swivel action for easier installation
- Neoprene rings hold silicon bronze bolts in place during installation
- Installed with ordinary wrench

Application

For Copper And Copperweld Conductors

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	400 - 800 kcmil
Conductor - Copper Str Run	• 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil • 800 kcmil
Conductor Type	CU C Str-Size
Conductor - Copper Str Tap Range	4/0 str. - 800 kcmil
Conductor - Copper Str Tap	• 4/0 AWG • 250 kcmil • 300 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	88.14 mm
Dimension - Height inch	3.47 in
Package Weight	0.000 lb.
Dimension - Width inch	2.72 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - Length Overall inch	2.31 in
Dimension - Stud Size inch	1/2 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

Plated	N
Trade Name	OKLIP™
Sub Brand	OKLIP
UPC	781810067802
Type	KVSW
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810067802
UPC 14 Digit GTIN	00781810067802

Logistics

Pallet Quantity	1
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)

- 350 kcmil
- 400 kcmil
- 450 kcmil
- 500 kcmil
- 550 kcmil
- 600 kcmil
- 700 kcmil
- 750 kcmil
- 800 kcmil



A Hubbell brand