



Substation - Aluminum Bolted T Connector

By Burndy
Catalog # [NNT22A18A](#)

Substation Connectors



Features

- Type NNT Aluminum T-Connectors for Aluminum and Copper Tube to Tube
- Properly proportioned to permit use on copper-aluminum conductor combinations
- Captured hex head bolts permit one-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Tube Std Run Range	4 IPS
Conductor - AL Tube Std Run	4 IPS
Conductor - Connection Combination	Tube to Tube
Conductor - AL Tube Std Tap Range	2 IPS
Conductor - AL Tube Std Tap	2 IPS
Conductor Type	• AL Tube Std-Run • AL Tube Std-Tap

Configuration

Physical Attribute - Pad Orientation	90 Degree
Physical Attribute - Number of Tap Conductors	1

Physical Attribute - Number of Run Conductors	1
Connector Type	T-Connector

Dimensions

Dimension - Height mm	157.2 mm
Dimension - Height inch	6.19 in
Dimension - Width mm	114 mm
Dimension - Width inch	4.50 in
Dimension - L Length Overall mm	276 mm
Dimension - B Length inch	6.00 in
Dimension - Length BB inch	4.25 in
Dimension - Length Overall inch	10.88 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

Plated	N
Material - Hardware	Aluminum
One Wrench Installation	Y
UPC	781810095140
Type	Bolted Tees
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810095140
UPC 14 Digit GTIN	00781810095140

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)