




LSC5561, AL Lightning Shield Clamp Assembly, 4/0 STR-556 AAC, 5.9 IN L, Galvanized Steel 3/8"-16 Eyebolt, insulation dia:1.34"



By Burndy
Catalog # [LSC5561](#)

Cast Al Alloy Lightning Shield Clamp Assembly, 4/0 STR-556 AAC, 5.9 IN L, Galvanized Steel 3/8"-16 Eyebolt, insulation dia:1.34"

Features

- Cast aluminum Lightning Shield Clamp
- Galvanized steel eye bolt for use on covered aluminum and ACSR primary overhead distribution conductors (tree wire)
- Designed to protect tree wire from burn-down causing service interruption during high lightning activity

Application

For Aluminum And ACSR Primary Covered Conductor (Tree Wire)

Specifications

Standards - RoHS Compliance Status	CM
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil
Conductor - AL Str Size Range	4/0 AWG-556 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - B Length fraction	1-1/2 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	150 mm
Dimension - B Length inch	1.5 in
Dimension - Length Overall inch	5.90 in

General

Plated	N
Material - Hardware	Galvanized Steel
Sub Brand	CONNECTOR
Oxide Inhibitor Type	Penetrox A-13
UPC	781810084960
Type	Arc Protection Device
Prefilled Oxide Inhibitor	Y
Material	Aluminum Alloy
Plating Type	Unplated
UPC 14 Digit GTIN	00781810084960

Logistics

Minimum Pack Quantity	40
Pallet Quantity	1800
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)